



Quickie SR45™
November 2021



EIZ9

Mark For:

Date: _____
 Dealer Acct #: _____
 Dealer: _____
 Dealer Contact: _____
 Dealer Address: _____
 Dealer City: _____ PV: _____ PC: _____
 Dealer Phone: () _____ Fax: () _____
 Confirmation Email: _____
 Confirm Via: Fax Email

Submitting for:

Quote Order

PO#: _____

ADDITIONAL SHIPPING INFORMATION

Ship To: _____
 Attention: _____
 Address: _____
 Address: _____
 Ship To City: _____ PV: _____ PC: _____
 Ship To Phone: () _____ Fax: () _____

Option #	Definition	Price	Option #	Definition	Price
----------	------------	-------	----------	------------	-------

1. FRAME

Base Model

<input type="checkbox"/>	194WM77	Quickie SR45	
--------------------------	---------	--------------	--

Frame Options

<input type="checkbox"/>	194FO3	Standard Base and Seat Frame Maximum Weight: 265 lbs.	
--------------------------	--------	--	--

Transit

<input type="checkbox"/>	194TO38	Transit Option	
--------------------------	---------	----------------	--

Tilt Release

<input type="checkbox"/>	194TT12	Backrest Dual Trigger Cable Release	
--------------------------	---------	-------------------------------------	--

Tilt Angle

<input type="checkbox"/>	194TA2	0° to 45°	
--------------------------	--------	-----------	--



Quickie SR45 shown with the JAY® J3™ backrest and JAY® 3™ cushion.



Quickie SR45 features IRIS™ (Intelligent Rotation In-Space) technology.

Option #	Definition	Price	Option #	Definition	Price
2. SIZE / SEATING					

Frame Width		
<input type="checkbox"/>	194W5	14"
<input type="checkbox"/>	194W6	15"
<input type="checkbox"/>	194W7	16"
<input type="checkbox"/>	194W8	17"
<input type="checkbox"/>	194W9	18"
<input type="checkbox"/>	194W10	19"
<input type="checkbox"/>	194W11	20"

Seat Type		
<input type="checkbox"/>	194ST35	Standard Seat Pan
<input type="checkbox"/>	194ST7	Omit Seat Pan



Frame Depth Set Up (Fill out either A or B)

A. Setup By QUICKIE

A. Desired Seat Depth

See **Figure 1**, Dimension A for measurement

<input type="checkbox"/>	194SD7	14"
<input type="checkbox"/>	194SD8	15"
<input type="checkbox"/>	194SD9	16"
<input type="checkbox"/>	194SD10	17"
<input type="checkbox"/>	194SD11	18"
<input type="checkbox"/>	194SD12	19"
<input type="checkbox"/>	194SD13	20"
<input type="checkbox"/>	194SD14	21"
<input type="checkbox"/>	194SD33	22"

A. User's Seated Height

See **Figure 1**, Dimension B. Distance from seat surface to top of the head.

<input type="checkbox"/>	194SJ01	Less than 37"
<input type="checkbox"/>	194SJ02	37" or Greater

B. Setup By DEPTH

B. Frame Depth Range


<input type="checkbox"/>	194FL91	Short Seat Frame 14"-18"
<input type="checkbox"/>	194FL92	Medium Seat Frame 16"-20"
<input type="checkbox"/>	194FL93	Long Seat Frame 18"-22"

B. Frame Depth

<input type="checkbox"/>	194FD5	14" <i>recommend short seat frame</i>
<input type="checkbox"/>	194FD6	15" <i>recommend short seat frame</i>
<input type="checkbox"/>	194FD7	16" <i>recommend short seat frame</i>
<input type="checkbox"/>	194FD8	17" <i>recommend short seat frame</i>
<input type="checkbox"/>	194FD9	18" <i>recommend medium seat frame</i>
<input type="checkbox"/>	194FD10	19" <i>recommend medium seat frame</i>
<input type="checkbox"/>	194FD11	20" <i>recommend long seat frame</i>
<input type="checkbox"/>	194FD16	21" <i>recommend long seat frame</i>
<input type="checkbox"/>	194FD17	22" <i>recommend long seat frame</i>

OR

Figure 1




A. Top of Cushion to Seat Rail

See **FIGURE 2** Dimensions A & B. This measurement is taken from the top of the cushion to the upper surface of the seat rail. If the cushion has a wedged shape and/or has significant lateral pelvic contour, then determine the height of the cushion at the point where the ischial tuberosities would contact (not immerse) the cushion surface.

<input type="checkbox"/>	194CJ04	2 1/2" or Greater
<input type="checkbox"/>	194CJ05	Less than 2 1/2"
<input type="checkbox"/>	194CJ03	Below Seat Rail

Figure 2



3. CASTERS / SEAT HEIGHT

Rear Wheel Size	CASTER SIZE					
	<input type="checkbox"/> 4	<input type="checkbox"/> 5	<input type="checkbox"/> 6	<input type="checkbox"/> 8x1	<input type="checkbox"/> 8x1.5	<input type="checkbox"/> 8x2
<input type="checkbox"/> 12" Low Poly	<input type="checkbox"/> 15.0					
	<input type="checkbox"/> 15.5	<input type="checkbox"/> 16.0				
	<input type="checkbox"/> 16.0	<input type="checkbox"/> 16.5				
	<input type="checkbox"/> 16.5	<input type="checkbox"/> 17.0				
<input type="checkbox"/> 22"	<input type="checkbox"/> 16.5	<input type="checkbox"/> 16.5				
	<input type="checkbox"/> 17.0	<input type="checkbox"/> 17.0		<input type="checkbox"/> 17.5		
	<input type="checkbox"/> 17.5	<input type="checkbox"/> 17.5	<input type="checkbox"/> 17.5	<input type="checkbox"/> 18.0	<input type="checkbox"/> 17.5	
	<input type="checkbox"/> 18.0	<input type="checkbox"/> 18.0	<input type="checkbox"/> 18.0	<input type="checkbox"/> 18.5		
<input type="checkbox"/> 24"	<input type="checkbox"/> 17.5	<input type="checkbox"/> 17.5	<input type="checkbox"/> 17.5	<input type="checkbox"/> 18.0		
	<input type="checkbox"/> 18.0	<input type="checkbox"/> 18.0	<input type="checkbox"/> 18.0	<input type="checkbox"/> 18.5	<input type="checkbox"/> 17.5	
	<input type="checkbox"/> 18.5	<input type="checkbox"/> 18.5	<input type="checkbox"/> 18.5	<input type="checkbox"/> 19.0	<input type="checkbox"/> 18.5	
	<input type="checkbox"/> 19.0	<input type="checkbox"/> 19.0	<input type="checkbox"/> 19.0	<input type="checkbox"/> 19.5		

Casters		
<input type="checkbox"/>	194CW34	6" Polyurethane
<input type="checkbox"/>	194CW35	6"x 1.5" Semi Pneumatic
<input type="checkbox"/>	194CW32	8" Polyurethane
<input type="checkbox"/>	194CW39	8"x 1.5" Semi Pneumatic

4. REAR WHEELS / SEAT HEIGHT

Rear Wheel		
<input type="checkbox"/>	194RW13	12" Mag Wheel
<input type="checkbox"/>	194RW8	22" Mag Wheel
<input type="checkbox"/>	194RW1	24" Mag Wheel

Rear Wheel Tire		
<input type="checkbox"/>	194RT3	Full Polyurethane N/A with 12" and 16"
<input type="checkbox"/>	194RT4	Low Polyurethane Only available with 12" Mag Wheel

Handrim		
<i>12" and 16" wheels not available with handrims.</i>		
<input type="checkbox"/>	194HR1	Aluminum Anodized
<input type="checkbox"/>	194HR7	Omit Handrim

Axle		
<input type="checkbox"/>	194AX1	Quick Release
<input type="checkbox"/>	194AX44	Threaded

5. WHEEL LOCKS

Wheel Lock		
<input type="checkbox"/>	194WL8	Push To Lock
<input type="checkbox"/>	194WL43	Rear Foot Operated Wheel Lock <i>*Only available with 12" rear wheels</i>
<input type="checkbox"/>	194WL10	Omit Wheel Lock

Wheel Lock Extension Handle		
<i>Not available with rear foot operated wheel lock</i>		
<input type="checkbox"/>	194EH7	Extension Handle (Pair)

6. HEADRESTS

Headrest & Bracket		
<input type="checkbox"/>		M2300 Bracket
<input type="checkbox"/>		Linx P1L Headrest

✓ Option # Definition Price ✓ Option # Definition Price

7. HANGER AND FOOTREST

Hanger			
<i>Front mount hangers only available w/ Alum angle adj footplates</i>			
<input type="checkbox"/>	194H140	70° Swing In/Swing Out -Front Mount	
<input type="checkbox"/>	194H142	80° Swing In/Swing Out -Front Mount	
<input type="checkbox"/>	194H161	Elevating Hanger - Front Mount <i>Only available w/ front mount alum angle adj footplates and 14"-22" width</i>	
<input type="checkbox"/>	194H144	Omit Hanger	

Hanger	Extension	Seat Sling to Top of Footrest		Min Allowable FSH
		Min	Max	
ELR Front Mount	No Ext (top hole)	3 1/2	7 1/2	5 1/2
	2" ext tube	7 1/4	10 1/4	9 1/4
	4" ext tube	9 1/4	12 1/4	11 1/4
	6" ext tube	11 1/4	14 1/4	13 1/4

Front Mount Extension Tubes (NA w/ Extension Mount Hangers)			
<i>Optional, not required for Front Mount Hangers</i>			
<input type="checkbox"/>	194E23	2"	
<input type="checkbox"/>	194E24	4" N/A w/14", 15" Seat To Floor Ht, N/A w/80° Hangers & 8" casters	

Hanger Mount			
Ext	None	2"	4"
70°	3.1" - 8.8"	3.1" - 11.1"	3.1" - 13.0"
80°	3.3" - 9.2"	3.3" - 11.7"	3.3" - 13.7"
90°	2.7" - 8.7"	2.7" - 11.2"	2.7" - 13.2"

Hanger Mount			
<input type="checkbox"/>	194MZ02	Standard Hanger Mount	
<input type="checkbox"/>	194MZ01	Offset Hanger Mount	

Footplates			
<i>Heel loop not included, see Footplate Options section below</i>			
<input type="checkbox"/>	194F1	Composite	
<input type="checkbox"/>	194F5	Aluminum <i>Only Avail w/ Elevating Legrest</i>	
<input type="checkbox"/>	194F291	Aluminium Angle Adjustable	J

Footplate Options			
<input type="checkbox"/>	194HL1	Heel Loops	
<input type="checkbox"/>	1945A02	Toe Loops (pair) <i>Only Avail w/ Angle Adj. Footplate</i>	

8. BACKREST / SEATING

Backrest Type			
<input type="checkbox"/>	194BT3	Non Folding Backrest <i>N/A with Height Adjustable Back</i>	
<input type="checkbox"/>	194BT99	Folding Backrest <i>N/A with Reclining Backrest</i>	

Backrest Options			
<input type="checkbox"/>	194OD19	Removable Extension <i>N/A with Height adj. back with adjustable stroller handle.</i>	


Backpost Style - Select only one option within A, B, or C

A. Stroller Handle Backpost (Fixed)			
<i>Folding Backrest adds 1" to the listed values.</i>			
<input type="checkbox"/>	194BP48	Low (18")	
<input type="checkbox"/>	194BP49	Medium (21")	
<input type="checkbox"/>	194BP50	Tall (24")	

B. Height Adjustable Back w/ Adj. Stroller Handles			
<input type="checkbox"/>	194BP51	Standard 15"-21"	
<input type="checkbox"/>	194BP52	Tall 18"-24"	

C. Reclining Backrest			
<i>Not available with 22" Deep Frame</i>			
<input type="checkbox"/>	194BP53	Medium (21")	See Dealer
<input type="checkbox"/>	194BP54	Tall (24")	See Dealer

JAY J3 Back			
<input type="checkbox"/>	194JB01	JAY J3 Back	



Option #	Definition	Price	Option #	Definition	Price
----------	------------	-------	----------	------------	-------

9. BACKREST / SEATING (CONT)

A. Backrest Position (set up by Quickie)

See **FIGURE 4** Dimension C. The location of the backrest surface in relation to the front of the backpost. The measurement is taken from the front surface of the backpost to the deepest area of the backrest in contact with the user's body.

<input type="checkbox"/>	194BQ01	+3"	
<input type="checkbox"/>	194BQ05	+2"	
<input type="checkbox"/>	194BQ02	+1"	
<input type="checkbox"/>	194BQ03	Flush	
<input type="checkbox"/>	194BQ04	-1"	
<input type="checkbox"/>	194BQ06	-2"	




Figure 4

Back Type	
1	3" forward (+3")
2	2" forward (+2")
3	1" forward (+1")
4	Flush
5	1" rearward (-1")
6	2" rearward (-2")

10. ARMREST / SIDEGUARDS

Armrest

Armrests w/ Transfer Bar N/A w/ 14" Seat Depth

<input type="checkbox"/>	194AA103	Dual Post Flip Back Height Adj w/Transfer Bar	
<input type="checkbox"/>	194AA104	Single Post Height Adjustable - Std	
<input type="checkbox"/>	194AA105	Single Post Height Adjustable - Low	
<input type="checkbox"/>	194AA14	Omit Armrest	

Armrest Matrix for Single Post


Armrest Size	Transfer Tube Length D	Receiver	H Range	Pad Length L	
				Desk	Full
STD	8"	STD	10 3/4" to 15 3/4"	10 1/4"	14"
		LOW	8 3/4" to 13 3/4"		
LOW	5 1/4"	STD	9" to 13"	10 1/4"	14"
		LOW	7 1/4" to 11 1/4"		

Armpad

<input type="checkbox"/>	194AM25	Desk	
<input type="checkbox"/>	194AM26	Full	

Armrest Receiver (Single Post Height Adjustable Only)

<input type="checkbox"/>	194AR17	Low	
<input type="checkbox"/>	194AR18	Std	



11. KEY OPTIONS AND ACCESSORIES

Anti Tips

<input type="checkbox"/>	194AT1	Anti Tips (Pair)	
--------------------------	--------	------------------	--

Positioning Belt

<input type="checkbox"/>	194A141	1.5" Auto Buckle Universal w/Clamp	
--------------------------	---------	------------------------------------	--

12. COLOR

Standard Frame Colors

<input type="checkbox"/>	194C2	Black (Not avail as base w/Zebra)	
--------------------------	-------	-----------------------------------	--

Additional Options Through Built for Me

To inquire about any unique customization for Quickie products, contact: Phone: (800) 263-3390, Fax: (800) 561-5834

